

Macro to Wide angle Lens 1 (MWL-1) Compatible Chart

		LENS		EXTENSION/ADAPTORS	LENS PORT	MAX. FOV	Remarks	
N120 Nikon System	APS-C	Nikon AF-S DX Micro NIKKOR 40mm f/2.8G DX	19152	N40G-F	18705 Macro port 44	150°	* Not compatible with wet macro lenses	
	FULL FRAME	Nikon AF-S Micro NIKKOR 60mm f/2.8G ED	19121	N60G-F	18701 Macro port 60	150°	* 1) Most recommended	
* Not compatible with Nikon AF-S Nikkor 105mm f/2.8G								
N85 M 4/3 System	APS-C	Olympus M.Zuiko Digital ED 30mm f3.5 Macro			36135 Macro port 45	150°	* Not compatible with wet macro lenses	
	M4/3 System	Panasonic Lumix G Macro 30mm f/2.8 Asph. Mega O.I.S.			36135 Macro port 45	150°	* Not compatible with wet macro lenses	
* Not compatible with Olympus 60mm f2.8 lens, Panasonic leica 45mm f2.8								
N85 Fujifilm (XT1 & XT2)	APS-C	Carl Zeiss Touit 2.8/50M	36422	36620 Mini extension ring 20	36135 Macro port 45	approx. 115°	* 1) Most recommended	
			XZ50-A	36630 Mini extension ring 30	36139 Macro Port 35	approx. 115°		
N100 XH1	APS-C	Carl Zeiss Touit 2.8/50M(X-mount)		37401 N100 Extension ring 30	37127 N100 Flat Port 32	approx. 115°	* 1) Most recommended	
				36471 N100 to N85 20mm port adaptor	36135 Macro port 45	approx. 115°		
N85 Sony E-Mount	Sony APS-C	Carl Zeiss Touit 2.8/50M		36630 Mini extension ring 30	36135 Macro port 45	approx. 115°	* 1) Most recommended	
Compact	Sony	Sony Cyber-shot DSC-RX100 III 17413 NA-RX100III				approx. 130°	Zoom from 65mm	
		Sony Cyber-shot DSC-RX100 IV 17415 NA-RX100IV				approx. 130°	Zoom from 65mm	
		Sony Cyber-shot DSC-RX100 V 17415 NA-RX100V				approx. 130°	Zoom from 65mm	
		Sony Cyber-shot DSC-RX100 VI 17415 NA-RX100VI			38703 N50 Short Port with Bayonet Mount	150°	* 1) Most recommended Zoom from 60 to 65mm	
	Canon	Canon PowerShot G7X 17318 NA-G7X housing					approx. 130°	Zoom from 65mm
		Canon PowerShot G7XII 17324 NA-G7XII Housing					approx. 130°	Zoom from 65mm
	Panasonic	Panasonic Lumix DMC-LX10 17414 NA-LX10 Housing					approx. 130°	Zoom from 65mm